

## Microwave drying sterilizer

Product Description: the use is widely used in the drying and sterilization of various bottles, flask, Xilin bottles and other glass containers in pharmaceutical production, which can be used for drying materials in industrial sectors such as chemical, food and electronics industries. Using the instructions and the upper gate, turn on the automatic heating button and adjust the upper and lower limits of the required temperature. When the thermostatic state is reached, turn on the transmission motor, adjust the transmission speed at the same time, open the fan and adjust the air volume. The material is loaded on stainless steel or aluminum plates on the chain or net belt. According to the technological requirements, temperature and speed can be adjusted at will to meet the requirements of drying and sterilization. This oven is made of 1Cr18Ni9Ti or imported SUS304 stainless steel plate. The conveyor belt is made of stainless steel chain or stainless steel mesh belt, and the speed of transmission is stepless speed regulation.